

Training Classes with Hands-on Experience

Level Instrumentation Fundamentals & Configuration

The Application Training Center

Your competent partner for application training in process automation.

The ATC provides

- Training with extensive hands-on experience
- Training under real process conditions
- Learning in small groups
- A didactical proven concept

Our training under real process conditions guarantees sustainable training success.

Location

The Application Training Center is located in Reinach, Switzerland.

Profit from a 'hands on experience' with training courses from the Application Training Center.



Hands-on lessons under real process conditions guarantee the best learning results

Select, configure and analyze level measuring principles for different applications

Course content Introduction to the basics of the most common level measuring principles and device configuration as well as operational parameters.

Installation suggestions for different level measurement principles will be discussed.

The right selection of the correct level measuring devices is also part of this training as well as the influence of the application and process conditions on the measurement stability and accuracy.

Key benefits Participants will understand: Hydrostatic, capacitive vibronic, radar, ultrasonic & guided radar measuring principles. They will be introduced to the device software in regards to parameters, signal curve, noise echo filtering and related information.

The participants learn to configure level measuring devices either on-site or remote with FieldCare, filter unwanted signal reflections and analyze the raw signal to understand applications and related measuring problems.

Process disturbances and how these disturbances effect the measurement accuracy are discussed.

Participants will be enabled to select the correct measuring principle for different applications and will get an awareness for the importance of application and process conditions for the measuring accuracy.



Experience real process conditions with our training rigs

Focus topics

- Introduction to different level measurement principles like microwave radar, guided radar, ultrasonic, hydrostatic, vibronic and capacitive measurement
- Introduction to different device parameters and configurations
- Typical applications for each measuring principle
- Installation suggestions

Target group Anyone who is interested in level measurement technologies as well as maintenance and project engineers for level applications

Working methods A combination of presentations and workshops, hands-on training in small groups (max. 4)

Minimum participants for a course: 4

Language English

Time

1. Day from 09:00am to 05:00pm
2. Day from 09:00am to 05:00pm
3. Day from 09:00am to 05:00pm

Location

Endress+Hauser Consult AG
Sales Support
Application Training Center
Kaegenstrasse 18
CH-4153 Reinach / Switzerland

Participation fee 2,400.- CHF
(including lunch and refreshments during coffee break)

Registration Online on www.endress.com or through email: atc@consult.endress.com

Application Training Center

Endress+Hauser Consult AG Sales Support
Kägenstrasse 18
4153 Reinach
Switzerland

Phone: +41617157700
Fax: +41617152888
atc@consult.endress.com
www.endress.com